Superplasma HI VIZ

ΚΛ/Κ US/CA



Technical Details

EXTERNAL SHELL: ABS Plastic HI VIZ INTERNAL SHELL: HD Polystyrene expanded HEADBAND: Soft PA Nylon headband (fixed to the external shell without metal rivets) SIZE: Universal-adjustable from 51 to 62 cm /20-24 3/8 Inches STANDARD: ANSÍ Z89.1 2014 / CSA Z94.1 2015 EN 12492 Shock Absorbing Capacity (clauses 4.2.1.2; 4.2.1.3; 4.2.1.4) TYPE 1 CLASS C









WHE00009 224

WHE00017.201





LIME FLUO

WHE00017.221 VELLOW FLUO



WHE00017.223



CSA: -30°C / +50°C -22°F / +122°F ANSI: -18°C / +49°C 0°F / +120°F

Technology



VENTILATION: Maximum ventilation thanks to the ten air intakes. The air intakes and the internal outflow channels guarantee effective breathability.

450g / 0.99 lb

FLUORESCENT SHELL: High visibility fluorescent color shell. Available in yellow fluo, white fluo, red fluo and lime fluo. The intensity of the luminescence color may decrease in time.



LUMINESCENT CLIPS: Helmet is equipped with strong external luminescent carrying clips, compatible with all headlamps with elastic bands on the market.

ECO LEATHER CHINSTRAP: Eco-leather, hypoallergenic, washable chinstrap which is extremely comfortable and helps avoid irritation of the skin.



REFLECTING STICKERS: Adhesive reflective stickers for high visibility.




ANTI-INTRUSION GRILLE: The air intakes are equipped with an anti-intrusion grille that prevents entry of debris whilst maintaining breathability.



RING TO HOOK: Fitted with a special hook on the chinstrap which allows the helmet to be connected to the harness.



SANITIZED®: The Sanitized® treatment is an antibacterial treatment that acts as an internal deodorant counteracting the development of unpleasant odors. Thanks to its hygienic function, it effectively prevents bacterial proliferation by increasing comfort of the fabric in contact with skin.





2DRY

UP & DOWN SYSTEM: The innovative and exclusive UP & Down technology ensures a precise and comfortable fit around the back of the head. A center wheel and two side arms allow quick adjustment of the helmet not only in width but also in height and tilt.



VISOR ATTACHMENT: Provided with attachment for visor installation. Compatible with all KASK



EARMUFFS FITTING: Built with bayonet adapter for earmuffs. Compatible with KASK earmuffs.

Superplasma HI VIZ



US/CA

Size Adjustment System

Up & Down size adjustment system gives the most precise and comfortable fitting thanks to its unique pivot design. Its mechanism consists of a central ratchet wheel that allows to dial in the tension and two lateral winglets for rapid and exact tuning of the size. This advanced size adjustment system offers increased stability of the helmet due to two additional adjustments of height and inclination, allowing correct positioning and ultimate fit of the helmet.



Additional Information



WARRANTY

3 years starting from the purchasing date.

SHELF LIFE

10 years starting from the production date (production date is printed on a label contained on the inside of the helmet). Inspect the helmet regularly to check for any damage! Cuts, abrasions, deformation or changes in colour represent important

elements for checking the helmet status.

CLEANING

Clean the helmet only with water, neutral pH soap and a soft, clean cloth. The inner lining should be washed by hand in cold water or in the washing machine (max 30°C - 85°F). Do not use chemical detergent or solvent.

STORAGE

When not in use the helmet should be stored away from direct sunlight or source of heat. ADHESIVE APPLICATION

Do not apply adhesives, solvents, stickers or paint that do not comply with the manufacturer's specifications. Any alteration or intervention not provided for may impair its protective function.

Accessories



WVI00002 VISOR V2



WAC00003 ADAPTER WITH BAYONET



WPA00003 REPLACEMENT INNER PADDING



LIPA00001 WINTER PADDING



WHP00001 EARMUFFS



HELMET BAG

NC 28208 - U.S.A. - T. 704 960 4851 - info@kaskamerica.us